

# AX-SXR System for Millwork & In-Wall

Greenguard US Patent # 5, 185, 818 FIA/TIA Compliant

The AX-SXR system allows an entire bay of equipment to pull out and rotate for easy installation and access to rear for servicing. The telescoping service stand and tracks disconnect for storage.

#### **Features**

- Rotation of rack allows for easy access to rear
- Rack can be mounted from 3" to 40" off floor
- Rack frame has 20" depth
- Detachable rack frame allows for off-site equipment integration
- Frame heights range from 15 spaces (26-1/4") to 43 spaces (75-1/4")
- Service stand is auick and simple to install
- Ball bearings allow smooth roll out
- 450 lb. weight capacity with proper weight distribution



**AX-SXR System shown** installed in millwork


# Architects' and Engineers' Specifications

Patented EIA compliant 19" roll-out equipment rack for millwork installation shall be Middle Atlantic Products model # AX-SXR(15 to 43 rackspaces). Rack shall have\_\_ useable rackspaces, overall height of ". (refer to chart) and a useable depth of 20". Rough-in millwork useable frame depth for installed components shall be from 25-1/2" to 27-1/2" depending on setback from millwork, and rack shall have a weight capacity of 450 lbs. Rack shall be constructed of the following materials: top, base, caster brackets, roller base, and horizontal braces shall be 13gauge steel with black powder coat finish, rack uprights shall be 11-gauge steel rackrail with tapped 10-32 mounting holes in universal EIA spacing. Rackrail shall be finished in black e-coat with marked rackspaces, top and bottom trim / locking panels shall lock AX-SXR in closed position and be 11-gauge aluminum with a black brushed and anodized finish. Rack top shall have openings to accept up to 2 fans, model # AXS-FAN (one fan) or AXS-FAN-K (two fans). Service tracks and stands shall be constructed of a 13-gauge steel frame with an aluminum extrusion. Service tracks for AX-SXR shall be model # TRACK31 with a 31" track length and 31" rack frame extension depth. Service stand shall be model #TRACKL (for 2-1/4" - 3-1/4" mounting height off floor), TS310 (for 3" - 11" mounting height off floor), TS1022 (for 10" - 22" mounting height

off floor) and TS1640 (for 16" - 40" mounting height off floor). AX-SXR shall be GREENGUARD Indoor Air Quality Certified for Children and Schools. AX-SXR shall be RoHS EU Directive 2002/95/EC compliant. Rack shall be manufactured by an ISO 9001 and ISO 14001 registered company. Rack shall be warrantied to be free from defects in material or workmanship for a period of 3 years.

- Optional slim fan for AX-SXR systems shall be model # AXS-FAN. Kit with 2 fans shall
- Optional full-depth 20" front and rear mount rackshelf shall be model # SH-5A
- Brush gasket shall require 19-5/8" rough-in opening width and shall be model # BG17
- Gasket and guide to center rack and protect millwork requires 19-5/8" rough-in opening width and shall be model # AXS-GG20

# **Specifications for AX-SXR System**



Part #		Extension Length	Frame Depth	Millwork Opening Depth
AX-SXR	-xx $^*$   Replace 'xx' with the # of useable rackspaces (15 to 43 space	s)   31 [787]	20 [508]	25-1/2 [648] to 27-1/2 [699] minimum

## **TOP VIEW TOP VIEW** (fully extended and rotated) 4-1/2 [114] 4-1/2 [114] minumum minumum clearance clearance for rotation for rotation **FRONT VIEW** 10X Ø.281 [7] 16.5 [419] 4X Ø.281 [7] X 1.125 [29] OB 2.00,[51] 9.625 [244] 18.00 [457] [241] 9.625 [244] 1!50 [38] 4X .75 [19] 1/2 [13] MIN. <sup>|-</sup>11.5 [292] 2 1/2 [63] MAX SET BACK


MILLWORK SPECIFICATIONS		
	A USEABLE HEIGHT	B MILLWORK OPENING HEIGHT
AX-SXR-15	26-1/4 [667] (15 spaces)	33 [838]
AX-SXR-16	28 [711] (16 spaces)	34-3/4 [883]
AX-SXR-17	29-3/4 [756] (17 spaces)	36-1/2 [927]
AX-SXR-18	31-1/2 [800] (18 spaces)	38-1/4 [972]
AX-SXR-19	33-1/4 [845] (19 spaces)	40 [1016]
AX-SXR-20	35 [889] (20 spaces)	41-3/4 [1060]
AX-SXR-21	36-3/4 [933] (21 spaces)	43-1/2 [1105]
AX-SXR-22	38-1/2 [978] (22 spaces)	45-1/4 [1149]
AX-SXR-23	40-1/4 [1022] (23 spaces)	47 [1194]
AX-SXR-24	42 [1067] (24 spaces)	48-3/4 [1238]
AX-SXR-25	43-3/4 [1111] (25 spaces)	50-1/2 [1283]
AX-SXR-26	45-1/2 [1156] (26 spaces)	52-1/4 [1327]
AX-SXR-27	47-1/4 [1200] (27 spaces)	54 [1372]
AX-SXR-28	49 [1245] (28 spaces)	55-3/4 [1416]
AX-SXR-29	50-3/4 [1289] (29 spaces)	57-1/2 [1461]
AX-SXR-30	52-1/2 [1334] (30 spaces)	59-1/4 [1505]
AX-SXR-31	54-1/4 [1378] (31 spaces)	61 [1549]
AX-SXR-32	56 [1422] (32 spaces)	62-3/4 [1594]
AX-SXR-33	57-3/4 [1467] (33 spaces)	64-1/2 [1638]
AX-SXR-34	59-1/2 [1511] (34 spaces)	66-1/4 [1683]
AX-SXR-35	61-1/4 [1556] (35 spaces)	68 [1727]
AX-SXR-36	63 [1600] (36 spaces)	69-3/4 [1772]
AX-SXR-37	64-3/4 [1645] (37 spaces)	71-1/2[1816]
AX-SXR-38	66-1/2 [1689] (38 spaces)	73-1/4 [1861]
AX-SXR-39	68-1/4 [1734] (39 spaces)	75 [1905]
AX-SXR-40	70 [1778] (40 spaces)	76-3/4 [1949]
AX-SXR-41	71-3/4 [1822] (41 spaces)	78-1/2 [1994]
AX-SXR-42	73-1/2 [1867] (42 spaces)	80-1/4 [2038]
AX-SXR-43	75-1/4 [1911] (43 spaces)	82 [2083]

# **Specifications for AX-SXR System**


All dimensions in inches unless otherwise noted [All bracketed dimensions are in millimeters]

#### **FRONT VIEW**

(AX-SXR inner frame)



#### **SETBACK**



#### NOTE:

To calculate rail to front edge clearance, use the numbers in "Millwork Specs" in conjunction with the clearance for any door or face you may provide for your millwork installation.

# **Millwork Specifications**

Part #	Width	Millwork Opening (see charts on page 2)  Rough Opening Height	Depth
AX-SXR*	19-1/4 [489] min.	, , ,	25-1/2 [648] to 27-1/2 [699] min.

<sup>\*</sup> When used with gasket and guide kit, millwork opening must be 19-5/8 [498] min.

Service Stands			
Part #	Height Range Off Of The Floor		
TRACKL	2-1/4 [57] to 3-1/4 [82]		
TS310	3 [76] to 11 [279]		
TS1022	10 [254] to 22 [559]		
TS1640	16[406] to 40 [1016]		

<u>Service Track</u>		
Part #	Track Length	
TRACK31	31 [787]	


Note: AX-SXR cannot be used with tracks of other lengths




# **Service Stands**

All dimensions in inches [Bracketed dimensions are in millimeters]


#### TRACKL with TRACK31



#### TS310 with TRACK31













TS1640 with TRACK31










Service Stands			
Part #	Height Range Off of the Floor		
TRACKL	2-1/4 [57] to 3-1/4 [82]		
TS310	3 [76] to 11 [279]		
TS1022	10 [254] to 22 [559]		
TS1640	16 [406] to 40 [1016]		





### Also available from Middle Atlantic Products

WR Series rotating roll-out enclosure, does not require tracks or stands for servicing, please see A&E specification # 96-01005.



AXS System factory-installed in Middle Atlantic Products steel cabinets, please see A&E Specification # 96-055S.



- For information on host cabinets, please see A&E Specification
- # 96-052SA (WRK-SA)
- # 96-039 (MRK)
- # 96-038 (ERK)